


**Transport equipment**

# Product data sheet

Article no.: 2435 Workshop cart with skirting



Modular system: Workshop cart in sectional/ tubular steel construction, powder-coated, blue RAL 5007. Surface out of beech plywood, 22 mm thick with skirting on 3 sides, 80 mm high. 1 additional shelf and 1 lockable steel cupboard with leaf-door, 1 fixed and 2 adjustable shelves. 500 mm wide, 600 mm deep and 600 mm high. Powder-coated, grey carcass RAL 7035, blue front RAL 5007. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

## Technical Details:



<b>Total load capacity (kg)</b>	400
<b>Length of usable platform (mm)</b>	1120
<b>Width of usable platform (mm)</b>	650
<b>Shelf heights (mm)</b>	226, 537, 850
<b>Total length (mm)</b>	1220
<b>Total width (mm)</b>	650
<b>Total height (mm)</b>	930
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	160 x 40
<b>Weight (kg)</b>	68
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976024356