


Transport equipment

Product data sheet

Article no.: 2441 Heavy table top cart



Modular system: Tubular steel and sectional steel, welded and powder coated, surface durably protected, resistant to impact and scratches. 3 shelves made of derived timber material boards, surface beech grain. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity upper and middle shelf 200 kg.

Technical Details:



Total load capacity (kg)	600
Length of usable platform (mm)	1000
Width of usable platform (mm)	600
Shelf heights (mm)	270, 585, 900, 1218
Total length (mm)	1197
Total width (mm)	609
Total height (mm)	1218
Tyres	TPE
Wheel size (mm)	200 x 40
Weight (kg)	78
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976424415