


Transport equipment

Product data sheet

Article no.: 2456/7016 Steel sheet workshop cart "GREY EDITION"



Sectional steel construction. Worktop composite panel grey 20 mm. With 1 cupboard with double door without separation wall. 2 adjustable shelves. Maximum opening angle 120°. Capacity per shelf 80 kg. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	400
Length of usable platform (mm)	985
Width of usable platform (mm)	590
Height of loading platform (mm)	915
Total length (mm)	1080
Total width (mm)	590
Total height (mm)	915
Tyres	TPE
Wheel size (mm)	160 x 40
Weight (kg)	48
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976424569