


Transport equipment

Product data sheet

Article no.: 2622 Light table top cart



Modular system: Tubular steel welded and powder coated, surface durably protected, resistant to impact and scratches. 2 shelves made of derived timber material boards, in a frame of angle steel, height of rim 12 mm. With 2 sheet steel drawers (H x W x D = 105 x 415 x 490 mm) with ball pull-out and cylinder lock. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity upper shelf 80 kg. Capacity per drawer 25 kg.

Technical Details:



Total load capacity (kg)	300
Length of usable platform (mm)	1000
Width of usable platform (mm)	600
Shelf heights (mm)	200, 820
Total length (mm)	1135
Total width (mm)	611
Total height (mm)	1040
Tyres	TPE
Wheel size (mm)	125 x 32
Weight (kg)	49
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976011516