


Transport equipment

Product data sheet

Article no.: 2474 Heavy workshop cart



Modular system: Steel tube and sectional steel welded, powder coated, surface durably protected, resistant to impact and scratches, platform made of derived timber material boards, surface beech grain. 1 centrally lockable drawer cupboard with 3 drawers 120 mm high and 1 drawer 180 mm high. Ball pull-out and pull-out stop. 4/5-pull-out. 500 mm wide, 700 mm deep and 600 mm high. Powder coated. Carcass grey RAL 7035, front blue RAL 5007. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Carrying capacity upper shelf 200 kg.

Technical Details:



Total load capacity (kg)	600
Length of usable platform (mm)	1050
Width of usable platform (mm)	700
Total length (mm)	1197
Total width (mm)	709
Total height (mm)	900
Tyres	TPE
Wheel size (mm)	200 x 40
Weight (kg)	89
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976024745