


Transport equipment

Product data sheet

Article no.: 2633 Light workshop cart



Tubular and sectional steel welded and powder coated, surface durably protected, resistant to impact and scratches, shelves made of derived timber material boards, in a frame of angle steel, height of rim 12 mm. 2 lockable steel cupboards with 1 fixed and 2 adjustable shelves, 500 mm wide, 600 mm deep and 600 mm high. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	300
Length of usable platform (mm)	1000
Width of usable platform (mm)	600
Height of loading platform (mm)	820
Total length (mm)	1130
Total width (mm)	600
Total height (mm)	1030
Tyres	TPE
Wheel size (mm)	125 x 32
Weight (kg)	69
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976011530