


**Transport equipment**

# Product data sheet

Article no.: 2940 Light table top cart



Modular system: Tubular steel welded and powder coated, surface durably protected, resistant to impact and scratches. 2 shelves made of derived timber material boards, in a frame of angle steel, height of rim 12 mm. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity upper shelf 80 kg.

## Technical Details:



|                                       |               |
|---------------------------------------|---------------|
| <b>Total load capacity (kg)</b>       | 300           |
| <b>Length of usable platform (mm)</b> | 850           |
| <b>Width of usable platform (mm)</b>  | 500           |
| <b>Shelf heights (mm)</b>             | 200, 820      |
| <b>Total length (mm)</b>              | 1021          |
| <b>Total width (mm)</b>               | 511           |
| <b>Total height (mm)</b>              | 830           |
| <b>Tyres</b>                          | TPE           |
| <b>Wheel size (mm)</b>                | 125 x 32      |
| <b>Weight (kg)</b>                    | 29            |
| <b>Country of origin</b>              | Germany       |
| <b>Warranty (years)</b>               | 10            |
| <b>Customs tariff number</b>          | 87168000      |
| <b>GTIN</b>                           | 4017976021263 |