


**Transport equipment**

# Product data sheet

Article no.: 2980 C+C cart



Tubular steel construction, powder coated, platform made of anti-skid waterproof plywood boards. With 2 lateral frames, 680 mm high, on the side of the fixed wheels also 2 lateral frames, 500 mm high. 2 swivel and 2 fixed-wheel castors, TPE tyres. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

## Technical Details:



<b>Total load capacity (kg)</b>	400
<b>Length of usable platform (mm)</b>	850
<b>Width of usable platform (mm)</b>	500
<b>Height of loading platform (mm)</b>	265
<b>Total length (mm)</b>	1045
<b>Total width (mm)</b>	643
<b>Total height (mm)</b>	949
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	160 x 40
<b>Weight (kg)</b>	28
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976029801