


Transport equipment

Product data sheet

Article no.: 2503B Open cart with platform made of sheet steel



Tubular steel and profile steel welded, powder coated, surface durably protected, resistant to impact and scratches. Platform made of sheet steel, flush with frame, welded powder coated RAL 5007. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	600
Length of usable platform (mm)	1200
Width of usable platform (mm)	800
Height of loading platform (mm)	270
Total length (mm)	1325
Total width (mm)	809
Total height (mm)	990
Tyres	TPE
Wheel size (mm)	200 x 40
Weight (kg)	42
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976525037