


Transport equipment

Product data sheet

Article no.: 3291 Mobile tilting stand



For plastic boxes, steel plate boxes, wire baskets etc., adjustable in height and mobile. Sectional steel-/ tubular construction with steel plate platform. Powder-coated blue RAL 5007. 4 swivel castors with TPE tyres, hubs with bush bearing, 2 swivel castors with wheel locks. Steel plate platform with single-sided lay-on edge, inclinable by 15° and 30°, continuously adjustable in height, rotatable and lockable, with pneumatic lowering damping.

Technical Details:



Total load capacity (kg)	150
Length of usable platform (mm)	510
Width of usable platform (mm)	410
Angle of inclination (degree)	0, 15, 30
Height adjustable from-to (mm)	720-1070
Tyres	TPE
Wheel size (mm)	75 x 25
Weight (kg)	28
Country of origin	Germany
Warranty (years)	2
Customs tariff number	94032080
GTIN	4017976032917