


**Transport equipment**

# Product data sheet

Article no.: 2632 Light workshop cart



Tubular and sectional steel welded and powder coated, surface durably protected, resistant to impact and scratches, shelves made of derived timber material boards, in a frame of angle steel, height of rim 12 mm. 3 platforms with all-round skirting, 12 mm high. 1 lockable steel cupboard with 1 fixed and 2 adjustable shelves, 500 mm wide, 600 mm deep and 600 mm high. Powder coated, grey carcass RAL 7035, blue front RAL 5007. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

## Technical Details:



<b>Total load capacity (kg)</b>	300
<b>Length of usable platform (mm)</b>	1000
<b>Width of usable platform (mm)</b>	600
<b>Shelf heights (mm)</b>	200, 510, 820
<b>Total length (mm)</b>	1130
<b>Total width (mm)</b>	600
<b>Total height (mm)</b>	1030
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	125 x 32
<b>Weight (kg)</b>	61
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976011523