


Transport equipment

Product data sheet

Article no.: 2722 Table top cart with trays



Modular system: Steel construction, welded. Tubular steel hoop and steel plate trays screwed. Trays oil-tight, rim 100 mm high, powder coated blue RAL 5007. Base with conical drain and drain tap 1/4". Grid with mesh width of 31 x 31 mm, loosely inserted, flush at the top. Lower steel plate tray 25 mm high, oil-tight. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity of upper shelf 100 kg.

Technical Details:



Total load capacity (kg)	300
Length of usable platform (mm)	1000
Width of usable platform (mm)	600
Shelf heights (mm)	181, 901
Total length (mm)	1136
Total width (mm)	611
Total height (mm)	1030
Tyres	TPE
Wheel size (mm)	125 x 32
Weight (kg)	52
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976027227