


**Transport equipment**

# Product data sheet

Article no.: 28102 Storeroom trolley



Sectional/tubular steel construction, completely electrolytically galvanised. End panels made of tubular steel of wire lattice, mesh width 100 x 50 mm, reinforced by 2 longitudinal bracings. Lower shelf fixed to base frame with wire lattice, mesh width 120 x 30 mm. 2 push bars on front side, vertically screwable. 4 smooth running swivel castors with TPE tyres with plastic rim, hubs with groove ball bearings and thread protection. 2 swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). 4 protective rings made of TPU (thermoplastic polyurethane) on the swivel castors.

## Technical Details:



<b>Total load capacity (kg)</b>	300
<b>Length of usable platform (mm)</b>	1250
<b>Width of usable platform (mm)</b>	610
<b>Height of loading platform (mm)</b>	193
<b>Load capacity per shelf (kg)</b>	80
<b>Total length (mm)</b>	1491
<b>Total width (mm)</b>	690
<b>Total height (mm)</b>	1225
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	125 x 32
<b>Weight (kg)</b>	28,3
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976281025