



Transport equipment

Product data sheet

Article no.: 28200 Storeroom trolley



Sectional/tubular steel construction, completely electrolytically galvanised. End panels made of tubular steel of wire lattice, mesh width 100 x 50 mm, reinforced by 2 longitudinal bracings. Lower shelf fixed to base frame with wire lattice, mesh width 120 x 30 mm. 2 push bars on front side, vertically screwable. 4 smooth running swivel castors with TPE tyres with plastic rim, hubs with groove ball bearings and thread protection. 2 swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). 4 protective rings made of TPU (thermoplastic polyurethane) on the swivel castors.

Technical Details:



Total load capacity (kg)	200
Length of usable platform (mm)	650
Width of usable platform (mm)	510
Height of loading platform (mm)	193
Load capacity per shelf (kg)	40
Total length (mm)	891
Total width (mm)	590
Total height (mm)	1625
Tyres	TPE
Wheel size (mm)	125 x 32
Weight (kg)	25
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976282008