


**Transport equipment**

# Product data sheet

Article no.: 4392 Box cart



Shelved trolley in angle steel construction with tubular handlebar. Ends, 1 side and top fitted with wire lattice 40 x 40 x 4 mm, completely welded and powder-coated. With 2-leaf door of angle steel with welded wire lattice on open side. 1 fixed and 4 detachable wood material shelves, surface beech grain. 2 swivel and 2 fixed-wheel castors with TPE tyres (thermoplastic elastomer), hubs with precision deep groove ball bearing. Maximum comfort: Very low starting, rolling and swivelling resistance. Low noise operation on level floors. Tyres are non-marking (trackless). TOTALSTOP central braking system standard on swivel castors. Clearance between shelves 280 mm. Capacity per shelf 90 kg.

## Technical Details:



<b>Total load capacity (kg)</b>	750
<b>Length of usable platform (mm)</b>	1000
<b>Width of usable platform (mm)</b>	680
<b>Shelf heights (mm)</b>	292, 582, 882, 1182, 1482
<b>Load capacity per shelf (kg)</b>	90
<b>Total length (mm)</b>	1170
<b>Total width (mm)</b>	740
<b>Total height (mm)</b>	1792
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	200 x 40
<b>Version</b>	Drahtgitter mit Stangenverschluss
<b>Weight (kg)</b>	154
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976043920