


**Transport equipment**

# Product data sheet

Article no.: 32911 Storage trolley



Tubular steel and steel section construction, powder coated. Upper and middle surface tiltable to both sides by 15° and 30°, locked by spring catch. With 3 platforms made of derived timber material boards, rim 10 mm high. Capacity upper and middle shelf 50 kg. 2 swivel and 2 fixed-wheel castors, TPE tyres, 125 x 32 mm, hubs with groove ball bearing. Swivel castors with wheel lock, according to European Standard EN1757-3 (safety of platform trolleys).

## Technical Details:



<b>Total load capacity (kg)</b>	200
<b>Length of usable platform (mm)</b>	605
<b>Width of usable platform (mm)</b>	405
<b>Shelf heights (mm)</b>	209, 664, 1164
<b>Load capacity per shelf (kg)</b>	50
<b>Total length (mm)</b>	821
<b>Total width (mm)</b>	455
<b>Total height (mm)</b>	1178
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	125 x 32
<b>Version</b>	Holzböden
<b>Weight (kg)</b>	33
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976013695