


**Transport equipment**

# Product data sheet

Article no.: 4703 Sheet metal dump truck without drainage tap



Made of 2 mm thick steel sheet, with double-folded top rim. Welded oil-tight. Chassis made of 3 mm thick canted steel sheet, with integrated stacker pockets. Kickplate and tilt lock, tubular steel handle. Powder coated blue RAL 5007. Fitted with 2 swivel and 2 fixed-wheel castors. Wheels with TPE tyres, 200 x 40 mm, hubs with groove ball bearing. Equipped as standard with TOTALSTOP - central brake system on swivel castors, according to the European Standard EN 1757-3 (safety of platform trolleys). Moveable by hand pushing and forklifters. Without drainage tap and sieve. Tipping process is triggered manually. For emptying with a forklift truck or for heavy loads, we recommend a tipping container or a self-tilting box.

## Technical Details:



<b>Total load capacity (kg)</b>	750
<b>Content (litres)</b>	600
<b>Box dimensions (mm)</b>	1321 x 794 x 735
<b>Dumping edge height with wheels (mm)</b>	843
<b>Total length (mm)</b>	1458
<b>Total width (mm)</b>	855
<b>Total height (mm)</b>	1099
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	200 x 40
<b>Version</b>	ohne Ablasshahn
<b>Weight (kg)</b>	95
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976047034