


**Transport equipment**

# Product data sheet

Article no.: 3742 Light table top cart



Modular system: Tubular steel welded and powder coated, surface durably protected, resistant to impact and scratches. 2 platforms: made of derived timber material boards, in a frame of angle steel, 1 shelf: height of rim 12 mm, 1 box: height of rim 45 mm. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity upper and middle shelf 80 kg. Inside dimension of box upper shelf: 965 x 555 x 45 mm.

## Technical Details:



<b>Total load capacity (kg)</b>	300
<b>Length of usable platform (mm)</b>	1000
<b>Width of usable platform (mm)</b>	600
<b>Shelf heights (mm)</b>	200, 820
<b>Total length (mm)</b>	1135
<b>Total width (mm)</b>	611
<b>Total height (mm)</b>	1040
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	125 x 32
<b>Weight (kg)</b>	34
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976037424