


**Transport equipment**

# Product data sheet

Article no.: 4704A/7016 Sheet metal dump truck with drainage tap "GREY EDITION"



Made of 2 mm thick steel sheet, with double-folded top rim. Welded oil-tight. Chassis made of 3 mm thick canted steel sheet, with integrated stacker pockets. Kickplate and tilt lock, tubular steel handle. Powder coated anthracite grey RAL 7016. Fitted with 2 swivel and 2 fixed-wheel castors. Wheels with elasticated solid rubber tyres 200 x 50 mm, blue-grey "trackless", hubs with ball bearing. Equipped as standard with TOTALSTOP - central brake system on swivel castors, according to the European Standard EN 1757-3 (safety of platform trolleys). Moveable by hand pushing and forklifters. With drainage tap and sieve. Tipping process is triggered manually. For emptying with a forklift truck or for heavy loads, we recommend a tipping container or a self-tilting box.

## Technical Details:



<b>Total load capacity (kg)</b>	800
<b>Content (litres)</b>	800
<b>Box dimensions (mm)</b>	1321 x 1044 x 735
<b>Dumping edge height with wheels (mm)</b>	843
<b>Total length (mm)</b>	1458
<b>Total width (mm)</b>	1105
<b>Total height (mm)</b>	1099
<b>Tyres</b>	Elastic solid rubber blue grey
<b>Wheel size (mm)</b>	200 x 50
<b>Version</b>	mit Ablasshahn
<b>Weight (kg)</b>	120
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976247045