


**Transport equipment**

# Product data sheet

Article no.: 4051 Hand cart



Made of tubular steel, welded and powder coated blue RAL 5007. Platform made of waterresistant plywood. With two ends 300 mm high and two insertable sides 220 mm high. Tubular steel frame with waterresistant plywood. Bogie steering with shaft and handle. Wheels with pneumatic tyretyres, hubs with roller bearings. Shaft with safety handle and with an automatic damped retraction in resting position. With automatic breaking system effective on the front wheels according to the European Standard EN 1757-3.

## Technical Details:



|  |                |
|--|----------------|
| <b>Total load capacity (kg)</b>        | 500            |
| <b>Length of usable platform (mm)</b>  | 1000           |
| <b>Width of usable platform (mm)</b>   | 550            |
| <b>Height of loading platform (mm)</b> | 308            |
| <b>Total length (mm)</b>               | 1272           |
| <b>Total width (mm)</b>                | 609            |
| <b>Total height (mm)</b>               | 1192           |
| <b>Tyres</b>                           | Pneumatic      |
| <b>Wheel size (mm)</b>                 | 260 x 85       |
| <b>Version</b>                         | mit Bordwänden |
| <b>Weight (kg)</b>                     | 39             |
| <b>Country of origin</b>               | Germany        |
| <b>Warranty (years)</b>                | 10             |
| <b>Customs tariff number</b>           | 87168000       |
| <b>GTIN</b>                            | 4017976440514  |