


Transport equipment

Product data sheet

Article no.: 4871 Office trolley



Modular system: bolted, tubular steel construction, powder coated light grey RAL 7035. Shelves and panels made of derived material timber board, pale grey. With longitudinal wall (back wall). 4 swivel castors with TPE tyres, hubs with roller bearings. 2 swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Flat packed for easy self assembly.

Technical Details:



Total load capacity (kg)	150
Length of usable platform (mm)	720
Width of usable platform (mm)	350
Shelf heights (mm)	260, 620, 980
Load capacity per shelf (kg)	50
Total length (mm)	810
Total width (mm)	385
Total height (mm)	1100
Tyres	TPE
Wheel size (mm)	125 x 32
Version	mit Rückwand
Weight (kg)	25
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976048710