


Transport equipment

Product data sheet

Article no.: 4122V Hand cart - 2 axles



Made of tubular steel, welded and powder coated. Rail 250 mm high, platform, sides and ends made of water-resistant plywood. Bogie steering with shaft and handle. Wheels with solid rubber tyres, hubs with roller bearings. Shaft with safety handle and with an automatic damped retraction in resting position. With automatic braking system effective on the front wheels according to the European Standard EN 1757-3.

Technical Details:



Total load capacity (kg)	400
Length of usable platform (mm)	945
Width of usable platform (mm)	545
Height of loading platform (mm)	307
Total length (mm)	1204
Total width (mm)	600
Total height (mm)	1185
Tyres	Solid rubber
Wheel size (mm)	250 x 60
Version	mit Bordwänden
Weight (kg)	44,7
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976741222