


**Transport equipment**

# Product data sheet

Article no.: 4878 Office trolley



Modular system: bolted, tubular steel construction, powder coated light grey RAL 7035. Shelves and panels made of derived material timber board, pale grey. With 2 separating plates and longitudinal wall (back wall), 4 swivel castors with TPE tyres, hubs with roller bearings. 2 swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Flat packed for easy self assembly.

## Technical Details:



<b>Total load capacity (kg)</b>	150
<b>Length of usable platform (mm)</b>	1080
<b>Width of usable platform (mm)</b>	350
<b>Shelf heights (mm)</b>	260, 620, 980
<b>Load capacity per shelf (kg)</b>	50
<b>Total length (mm)</b>	1165
<b>Total width (mm)</b>	385
<b>Total height (mm)</b>	1100
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	125 x 32
<b>Version</b>	mit Rückwand und Trennwänden
<b>Weight (kg)</b>	34
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976048789