


Transport equipment

Product data sheet

Article no.: 4922 Table top cart with trays



Modular system: Steel construction, welded. Tubular steel hoop and steel plate trays screwed. Trays oil-tight, rim 40 mm high, powder coated blue RAL 5007. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity of upper shelf 200 kg.

Technical Details:



Total load capacity (kg)	400
Length of usable platform (mm)	1000
Width of usable platform (mm)	700
Shelf heights (mm)	248, 870
Total length (mm)	1136
Total width (mm)	700
Total height (mm)	1105
Tyres	TPE
Wheel size (mm)	200 x 40
Weight (kg)	50
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976049229