


**Transport equipment**

# Product data sheet

Article no.: 5005 Stainless steel trolley



Stainless steel trolley (tea-cart) with tubular push bar made of CNS (chrome-nickel steel) and 3 deep-drawn shelves made of CS (chrome steel), with all-round skirting, lined for sound reduction. Capacity per shelf 80 kg. 4 swivel castors with TPE wheels, elastic and easy running, trackless. Hubs with ball bearings, 2 swivel castors with wheel locks according to the European Standard EN 1757-3 (safety of platform trolleys). Rustproof wheels according to DIN 18867 part 8. For preventing large damages with protective edges and protective wheels. Flat packed for easy self assembly.

## Technical Details:



<b>Total load capacity (kg)</b>	150
<b>Shelf heights (mm)</b>	230, 540, 850
<b>Length of usable platform (mm)</b>	800
<b>Width of usable platform (mm)</b>	500
<b>Total length (mm)</b>	870
<b>Total width (mm)</b>	570
<b>Total height (mm)</b>	950
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	125 x 32
<b>Weight (kg)</b>	17
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976050058