


**Transport equipment**

# Product data sheet

Article no.: 5592 Box cart



Box cart in angle steel construction with tubular handlebar, powder coated. Ends, side, folding door and roof covered with 1,5 mm aluminium sheet. Double wing door made of angle steel with vertical locking rod and integrated cylinder lock. 1 fixed and 4 detachable wood material shelves, surface beech grain. 2 swivel and 2 fixed-wheel castors with TPE tyres (thermoplastic elastomer), hubs with precision deep groove ball bearing. Maximum comfort: Very low starting, rolling and swivelling resistance. Low noise operation on level floors. Tyres are non-marking (trackless). TOTALSTOP central braking system standard on swivel castors. Clearance between shelves 280 mm. Capacity per shelf 90 kg.

## Technical Details:



<b>Total load capacity (kg)</b>	750
<b>Length of usable platform (mm)</b>	1000
<b>Width of usable platform (mm)</b>	680
<b>Shelf heights (mm)</b>	292, 582, 882, 1182, 1482
<b>Load capacity per shelf (kg)</b>	90
<b>Total length (mm)</b>	1170
<b>Total width (mm)</b>	745
<b>Total height (mm)</b>	1792
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	200 x 40
<b>Version</b>	Alublech mit Treibriegelverschluss
<b>Weight (kg)</b>	141
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976013169