


**Transport equipment**

# Product data sheet

Article no.: 5838-IS1 Rolling desk with equipment for infection protection



Steel tube and sectional steel welded, bolted construction, powder coated blue RAL 5007. Surface made of derived timber material, 1100 mm wide und 589 mm deep, with stop bar. With 1 lockable steel cupboard (W x D x H: 500 x 600 x 600 mm) with leaf-door. 1 fixed and 2 adjustable shelves. Powder coated carcass RAL 7035, blue front RAL 5007. Capacity per shelf in cupboards 30 kg. 4 swivel castors with TPE tyres 125 x 32 mm, 2 swivel castors with wheel locks, hubs with plain bearings. Easy movement across angles and barriers because of the big wheels. Also equipped with infection protection frame 5942, disinfectant holder 1393-B0500 (for 500 ml Bode bottle) and spray bottle holder 1391. Bottles not included in the delivery.

## Technical Details:



<b>Total load capacity (kg)</b>	100
<b>Surface height (mm)</b>	1100/1195
<b>Length of usable platform (mm)</b>	1000
<b>Width of usable platform (mm)</b>	600
<b>Total width (mm)</b>	1105
<b>Total depth (mm)</b>	659
<b>Total height (mm)</b>	2305
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	125 x 32
<b>Weight (kg)</b>	71,2
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	94032080
<b>GTIN</b>	4017976858388