


Transport equipment

Product data sheet

Article no.: 6230 Tipping container without drainage tap



Particularly low construction. Tipping containers must be lifted with a fork lift for emptying. By dropping the box to the ground the container will be adjusted automatically and moved back into loading position. Sturdy welded 2 mm sheet steel design, powder coated in RAL 5007 blue. Standard-fitted fork-lift sleeves, anti-roll safety device and tilt lock. Safety chain as anti-skidding and safety device. Traction cable to activate tilting mechanism, operated from fork-lift truck driver's seat. Item number with addition "A" means "with drainage tap".

Technical Details:



| | |
|--|------------------|
| Total load capacity (kg) | 750 |
| Content (litres) | 300 |
| Box dimensions (mm) | 1088 x 630 x 498 |
| Dumping edge height without wheels (mm) | 418 |
| Dumping edge height with wheels (mm) | 655 |
| Total length (mm) | 1313 |
| Total width (mm) | 690 |
| Total height (mm) | 576 |
| Version | ohne Ablasshahn |
| Weight (kg) | 78 |
| Country of origin | Germany |
| Warranty (years) | 10 |
| Customs tariff number | 73101000 |
| GTIN | 4017976166230 |