


Transport equipment

Product data sheet

Article no.: 4822/7016 Table top cart with trays "GREY EDITION"



Modular system: Steel construction, welded. Tubular steel hoop and steel plate trays screwed. Trays oil-tight, rim 40 mm high, powder coated anthracite grey RAL 7016. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity of upper shelf 200 kg.

Technical Details:



Total load capacity (kg)	400
Length of usable platform (mm)	1000
Width of usable platform (mm)	700
Shelf heights (mm)	248, 870
Total length (mm)	1171
Total width (mm)	700
Total height (mm)	910
Tyres	TPE
Wheel size (mm)	200 x 40
Weight (kg)	47
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976748221