


Transport equipment

Product data sheet

Article no.: 6250A Tipping container with drainage tap



Particularly low construction. Tipping containers must be lifted with a fork lift for emptying. By dropping the box to the ground the container will be adjusted automatically and moved back into loading position. Sturdy welded 2 mm sheet steel design, powder coated in RAL 5007 blue. Standard-fitted fork-lift sleeves, anti-roll safety device and tilt lock. Safety chain as anti-skidding and safety device. Traction cable to activate tilting mechanism, operated from fork-lift truck driver's seat. Item number with addition "A" means "with drainage tap".

Technical Details:



Total load capacity (kg)	1000
Content (litres)	500
Box dimensions (mm)	1164 x 831 x 598
Dumping edge height without wheels (mm)	519
Dumping edge height with wheels (mm)	756
Total length (mm)	1389
Total width (mm)	890
Total height (mm)	676
Version	mit Ablasshahn
Weight (kg)	87
Country of origin	Germany
Warranty (years)	10
Customs tariff number	73090090
GTIN	4017976662503