


Transport equipment

Product data sheet

Article no.: 5392/7016 Box cart "GREY EDITION"



Shelved trolley in angle steel construction with tubular handlebar. Ends, 1 side and top fitted with wire lattice 40 x 40 x 4 mm, completely welded and powder-coated. With 2-leaf door of angle steel with welded wire lattice on open side. 1 fixed and 4 detachable wood material shelves, surface grey. 2 swivel and 2 fixed-wheel castors with TPE tyres (thermoplastic elastomer), hubs with precision deep groove ball bearing. Maximum comfort: Very low starting, rolling and swivelling resistance. Low noise operation on level floors. Tyres are non-marking (trackless). TOTALSTOP central braking system standard on swivel castors. Clearance between shelves 280 mm. Capacity per shelf 90 kg.

Technical Details:



Total load capacity (kg)	750
Length of usable platform (mm)	1000
Width of usable platform (mm)	680
Shelf heights (mm)	292, 582, 882, 1182, 1482
Load capacity per shelf (kg)	90
Total length (mm)	1170
Total width (mm)	745
Total height (mm)	1792
Tyres	TPE
Wheel size (mm)	200 x 40
Version	Drahtgitter mit Treibriegelverschluss
Weight (kg)	144
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976253923