


Transport equipment

Product data sheet

Article no.: 6453LZ Hand truck



Modular system: Made of welded sectional steel, powder coated blue RAL 5007. Surface durably protected, resistant to impact and scratches, 4 tubular sleeves at corners. Boogie steered by crown gear, scissors-shaped shaft with safety handle with soft rubber grip and with an automatic damped retraction in resting position. Platform of anti-slipping, waterproof plywood. Wheels with pneumatic tyres, hubs with roller bearings. With automatic braking system effective on the front wheels according to the European Standard EN 1757-3. Boards 250/325 mm high, 3 sides tilting, front end fixed. Powder coated tubular steel frame with waterproof plywood platform.

Technical Details:



Total load capacity (kg)	750
Length of usable platform (mm)	1200
Width of usable platform (mm)	800
Height of loading platform (mm)	420
Total length (mm)	1560
Total width (mm)	825
Total height (mm)	1130
Tyres	Pneumatic
Wheel size (mm)	260 x 85
Version	mit Bordwänden
Weight (kg)	78
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976214092