


**Transport equipment**

# Product data sheet

Article no.: 6446L Hand truck



Modular system: Made of welded sectional steel, powder coated blue RAL 5007. Surface durably protected, resistant to impact and scratches, 4 tubular sleeves at corners. Boogie steered by crown gear, scissors-shaped shaft with safety handle with soft rubber grip and with an automatic damped retraction in resting position. Platform of anti-slipping, waterproof plywood. Wheels with pneumatic tyres, hubs with roller bearings. With automatic braking system effective on the front wheels according to the European Standard EN 1757-3. Boards 1000 mm high, sides screwed on platform, Sides mountable and removable. Tubular steel frame with welded wire lattice 40 x 40 x 4 mm, powder coated blue RAL 5007.

## Technical Details:



<b>Total load capacity (kg)</b>	1250
<b>Length of usable platform (mm)</b>	2000
<b>Width of usable platform (mm)</b>	1000
<b>Height of loading platform (mm)</b>	490
<b>Total length (mm)</b>	2350
<b>Total width (mm)</b>	1050
<b>Total height (mm)</b>	1490
<b>Tyres</b>	Pneumatic
<b>Wheel size (mm)</b>	400 x 100
<b>Version</b>	mit Drahtgitterwänden
<b>Weight (kg)</b>	155
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976446011