


Transport equipment

Product data sheet

Article no.: 6821 Skid lifter



Excellent stability under load and travelling even with lifted load. Frame and forks made in sectional steel construction, powder coated, anthracite grey RAL 7016. Sturdy tubular push handle. Hydraulic pump with chromium-plated piston and overload valve. Operated via pedal control. Lowering valve to be operated via hand lever. 2 castor wheels with lock. Version is additionally equipped with a steering shaft.

Technical Details:

Total load capacity (kg)	1000
Total length (mm)	1640
Total width (mm)	687
Lifting range (mm)	85 - 830
Fork length (mm)	1115
Fork width (m)	153
Loading width (mm)	526
Tyres	Polyurethane
Wheel size (mm)	150 x 40
Material fork rollers	Nylon tandem
Fork rollers diameter x width (mm)	70 x 70
Weight (kg)	135
Country of origin	China
Warranty (years)	2
Customs tariff number	84279000
GTIN	4017976068213