


Transport equipment

Product data sheet

Article no.: 6852 Hand winch stacker



For the occasional use as lifting and transport appliance. Sturdy sectional steel construction with tubular push handles, powder coated anthracite RAL 7016. Maintenance free. Lifting by means of safety hand winch. Forks adjustable. 2 castor wheels, wheels with Polyurethane tyres 150 x 40 mm and 2 fork rollers nylon 80 x 47 mm. Castor wheels with lock. Load center distance: 400 mm, stroke per crank turning: 40 mm, total height 2030 mm.

Technical Details:

Total load capacity (kg)	500
Total length (mm)	1550
Total width (mm)	725
Total height (mm)	2030
Lifting range (mm)	90 - 1560
Fork length (mm)	1000
Fork width (m)	80
Loading width (mm)	170-690
Tyres	Polyurethane
Wheel size (mm)	150 x 40
Material fork rollers	Nylon
Fork rollers diameter x width (mm)	80 x 47
Weight (kg)	146
Country of origin	China
Warranty (years)	2
Customs tariff number	84279000
GTIN	4017976068527