


Transport equipment

Product data sheet

Article no.: 71252 Swivel castor

Casings made of steel sheet, galvanized. Wheels with elastic tyres, blue-grey, non-marking (trackless). Alu-rims, hubs with ball bearings. Smooth, silent running, long durability.



Technical Details:

Total load capacity (kg)	200
Wheel size (mm)	125 x 40
Tyres	Elastic solid rubber blue grey
Effective height (mm)	165
Mounting plate (mm)	105 x 80
Screw hole distances (mm)	80/76 x 60
Screw hole-Ø (mm)	9
Weight (kg)	1,4
Country of origin	China
Warranty (years)	10
Customs tariff number	73269098
GTIN	4017976371252