


**Transport equipment**

# Product data sheet

Article no.: 71272 Fixed-wheel castor

Casings made of steel sheet, galvanized. Wheels with elastic tyres, blue-grey, non-marking (trackless). Alu-rims, hubs with ball bearings. Smooth, silent running, long durability.



## Technical Details:

<b>Total load capacity (kg)</b>	200
<b>Wheel size (mm)</b>	125 x 40
<b>Tyres</b>	Elastic solid rubber blue grey
<b>Effective height (mm)</b>	165
<b>Mounting plate (mm)</b>	105 x 80
<b>Screw hole distances (mm)</b>	80/76 x 60
<b>Screw hole-Ø (mm)</b>	9
<b>Weight (kg)</b>	1,22
<b>Country of origin</b>	China
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	73269098
<b>GTIN</b>	4017976712727