


Transport equipment

Product data sheet

Article no.: 6837 Lifting table cart



Sectional steel/steel plate construction, powder coated anthracite RAL 7016. Sturdy tubular push handle. Hydraulic pump with chromium-plated piston. Operation via pedal control. Lowering valve precisely adjustable via hand lever. 2 castor and 2 fixed wheels, wheels with Polyurethane tyres, castor wheels with lock. Double shears for enlarged lifting range. Tubular push handle fixed with screws.

Technical Details:

Total load capacity (kg)	500
Lifting range (mm)	440 - 1575
Length of usable platform (mm)	1010
Width of usable platform (mm)	520
Total length (mm)	1275
Total width (mm)	520
Tyres	Polyurethane
Wheel size (mm)	150
Weight (kg)	168
Country of origin	China
Warranty (years)	2
Customs tariff number	84279000
GTIN	4017976068374