


**Transport equipment**

# Product data sheet

Article no.: 6851 Hand winch stacker



For the occasional use as lifting and transport appliance. Sturdy sectional steel construction with tubular push handles, powder coated anthracite RAL 7016. Maintenance free. Lifting by means of safety hand winch. Forks adjustable. 2 castor wheels, wheels with Polyurethane tyres 150 x 40 mm and 2 fork rollers nylon 80 x 47 mm. Castor wheels with lock. Load center distance: 400 mm, stroke per crank turning: 40 mm, total height 2030 mm.

## Technical Details:

<b>Total load capacity (kg)</b>	250
<b>Total length (mm)</b>	1350
<b>Total width (mm)</b>	725
<b>Total height (mm)</b>	2030
<b>Lifting range (mm)</b>	90 - 1560
<b>Fork length (mm)</b>	800
<b>Fork width (m)</b>	75
<b>Loading width (mm)</b>	170-690
<b>Tyres</b>	Polyurethane
<b>Wheel size (mm)</b>	150 x 40
<b>Material fork rollers</b>	Nylon
<b>Fork rollers diameter x width (mm)</b>	80 x 47
<b>Weight (kg)</b>	140
<b>Country of origin</b>	China
<b>Warranty (years)</b>	2
<b>Customs tariff number</b>	84279000
<b>GTIN</b>	4017976068510