


Transport equipment

Product data sheet

Article no.: 71614 Swivel castor with lock

Casings made of steel sheet, galvanized. Plastic rims, hubs with ball bearing and thread protection. Very low starting, rolling and swivelling resistance. Wheels non-marking (trackless).



Technical Details:

Total load capacity (kg)	250
Wheel size (mm)	200 x 40
Tyres	TPE
Effective height (mm)	237
Mounting plate (mm)	135 x 110
Screw hole distances (mm)	105 x 75/80
Screw hole-Ø (mm)	11
Weight (kg)	2,8
Country of origin	China
Warranty (years)	10
Customs tariff number	73269098
GTIN	4017976716145