


Transport equipment

Product data sheet

Article no.: 6856 Hydraulic hand stacker



For the occasional use as lifting and transport appliance. Sturdy sectional steel construction with tubular push handles, powder coated anthracite RAL 7016. Hydraulic pump with chromiumplated piston and overload valve. Operated via drawing shaft. Lowering valve precisely adjustable via hand lever. 2 castor wheels, wheels with Polyurethane tyres 150 x 40 mm and 2 fork rollers nylon 80 x 70 mm. Castor wheels with lock. Load center distance: 585 mm, stroke per shaft operation: 20 mm, total height: 2010 mm.

Technical Details:

Total load capacity (kg)	1000
Total length (mm)	1600
Total width (mm)	794
Total height (mm)	2010
Lifting range (mm)	88 - 1500
Fork length (mm)	1150
Fork width (m)	160
Loading width (mm)	540
Tyres	Polyurethane
Wheel size (mm)	150 x 40
Material fork rollers	Nylon
Fork rollers diameter x width (mm)	80 x 70
Weight (kg)	220
Country of origin	China
Warranty (years)	2
Customs tariff number	84279000
GTIN	4017976068565