


Transport equipment

Product data sheet

Article no.: 71522 Fixed-wheel castor

Casings made of steel sheet, galvanized. polyamide wheels, hubs with roller bearings. Largely resisting to humidity, salt, acids and caustic solutions. Temperature-resistant from -40° to +90° C.



Technical Details:

Total load capacity (kg)	200
Wheel size (mm)	125 x 38
Tyres	Polyamide
Effective height (mm)	165
Mounting plate (mm)	105 x 80
Screw hole distances (mm)	80/76 x 60
Screw hole-Ø (mm)	9
Weight (kg)	0,82
Country of origin	China
Warranty (years)	10
Customs tariff number	73269098
GTIN	4017976016825