


**Transport equipment**

# Product data sheet

Article no.: 71624 Fixed-wheel castor

Casings made of steel sheet, galvanized. Plastic rims, hubs with ball bearing and thread protection. Very low starting, rolling and swivelling resistance. Wheels non-marking (trackless).



## Technical Details:

<b>Total load capacity (kg)</b>	250
<b>Wheel size (mm)</b>	200 x 40
<b>Tyres</b>	TPE
<b>Effective height (mm)</b>	237
<b>Mounting plate (mm)</b>	135 x 110
<b>Screw hole distances (mm)</b>	105 x 75/80
<b>Screw hole-Ø (mm)</b>	11
<b>Weight (kg)</b>	1,7
<b>Country of origin</b>	China
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	73269098
<b>GTIN</b>	4017976716244