


Transport equipment

Product data sheet

Article no.: 9381 ESD-euro box trolley



Electrostatic discharge construction (ESD = Electrostatic Discharge). Tubular steel and sectional steel welded, conductive powder coating, slate grey, RAL 7015. Wheels electrically conductive (anti-static) with TPE-ESD tyres (thermoplastic elastomer). Hubs with precision deep groove ball bearing. Castors with wheel lock, according to the European Standard EN 1757-3 (safety of platform trolleys). 3 platforms with shelves made of electrically conductive (antistatic) wooden material according to DIN 68765, light grey, rim 7 mm high. For 1 Euro box each 600 x 400 mm. Variable use of shelf frames, distance 50 mm, angle when inclined up to 15° and 30°. Capacity per shelf 80 kg.

Technical Details:



Total load capacity (kg)	250
Length of usable platform (mm)	410
Width of usable platform (mm)	610
Shelf heights (mm)	264, 564, 864
Load capacity per shelf (kg)	80
Total length (mm)	525
Total width (mm)	666
Total height (mm)	1101
Tyres	TPE-ESD
Wheel size (mm)	125 x 32
Weight (kg)	41
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976493817