


Transport equipment

Product data sheet

Article no.: 9392 ESD-Box cart



ESD-box cart in angle steel construction with tubular handlebar. Ends, 1 side and top fitted with wire lattice 40 x 40 x 4 mm, completely welded and electrically conductive powder-coated, slate grey RAL 7015. With 2-leaf door of angle steel with welded wire lattice on open side. 1 fixed and 4 detachable shelves made of electrically conductive wooden material according to DIN 68765, light grey. 2 swivel and 2 fixed-wheel castors with ESD-TPE tyres (thermoplastic elastomer), electrically conductive, hubs with precision deep groove ball bearing. Maximum comfort: Very lowstarting, rolling and swivelling esistance. Low noise operation on level floors. Tyres are non-marking (trackless). TOTALSTOP central braking system standard on swivel castors.

Technical Details:



Total load capacity (kg)	750
Length of usable platform (mm)	1000
Width of usable platform (mm)	680
Shelf heights (mm)	292, 582, 882, 1182, 1482
Load capacity per shelf (kg)	50
Total length (mm)	1170
Total width (mm)	745
Total height (mm)	1792
Tyres	TPE-ESD
Wheel size (mm)	200 x 40
Weight (kg)	144
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976993928