

TECHNICAL DATA SHEET

CARL S3 HI No. 64461

Sz. 39 - 48



LABELLING ACCORDING TO STANDARD

Standard for safety footwear EN ISO 20345:2022 S3	Basic requirement for S3: A Antistatic shoe - E Energy absorption in the heel - FO Fuel resistance - WPA Water penetration and absorption - P Penetration resistance - Closed heel area - Profiled outsole
Additional requirements	<p>HI HEAT INSULATED</p> <p>HRO HEAT RESISTANT OUTSOLE Heat resistance against contact heat, also during short-term high temperatures</p> <p>FO FUEL RESISTANCE</p> <p>SR Slip resistance on ceramic tile with glycerine.</p> <p>SC SCUFF CAP The overcap manages a certain amount of abrasion.</p> <p>LG LADDER GRIP Heel edge of at least 10 mm</p>


FORM

<p>Safety boot</p>	Form B - in size 42, the upper height must be at least 11.3 cm.
--------------------	---

AREAS OF APPLICATION

Areas of application	<p>Indoors and outdoors</p> <p>Areas where exposure to moisture is expected (S2)</p> <p>Areas where there is a risk of penetration from pointed and sharp objects (S3)</p> <p>Hot zones where high demands are placed on the sole for heat resistance E.g. foundries, welding works etc.</p>
----------------------	--

FEATURES

Certification in accordance with DGUV rule 112-191	<ul style="list-style-type: none"> • Certified for orthopaedic inserts 
Bellows tongue	<ul style="list-style-type: none"> • Excellent wearing comfort: The tongue avoids dirt from entering into the shoe.
Collar padding	<ul style="list-style-type: none"> • Excellent wearing comfort: the ankle-wrapping, softly padded upper edge provides for stability and grip in the shoe.
Buckle	<ul style="list-style-type: none"> • Allows straps to be set individually
Strong rivet in the area of the well-worn leather upper	The reinforcement rivet reduces the strain on the seams and provides for an extended durability of the uppers.
Padded protective collar	<ul style="list-style-type: none"> • Additional protection: The collar prevents dirt and other foreign objects from entering into the shoe.
Seams made of heat-resistant thread	<ul style="list-style-type: none"> • Best possible protection against flames, heat and chemicals. Cleaning does not affect the heat resistance.
Quick release fastener	<ul style="list-style-type: none"> • Allows shoes to be removed with one hand in the case of danger • The tongue can be adjusted by means of a buckle
PU toe protection (polyurethane)	<ul style="list-style-type: none"> • Directly applied tip protection • Excellent wear protection in the shoe tip area • Protects the upper material in this area against premature wear


UPPER MATERIAL

Cowhide leather	<ul style="list-style-type: none"> • Areas of application S1/S2/S3 • Natural material • Wear-resistant • Breathable • Water penetration/absorption in accordance with EN ISO 20345 S2
-----------------	--

LINING


Leather lining	<ul style="list-style-type: none"> • High tear resistance • Breathable • Natural material
Heel pocket lining	<ul style="list-style-type: none"> • The abrasion-resistant microfibre material is particularly sturdy and provides for a pleasant wearing comfort.

TOE PROTECTION CAP

<p>Steel toe cap</p> 	<ul style="list-style-type: none"> • Protection against impacts of min. 200 joules and pressure loading of min. 15 kN • Permanent edge coverage for cushioning • Ergonomically shaped • Comfortable toe room • Good coverage of the little toe area
--	--

INLAY SOLE

Full-length inlay sole
BASIC



- The full-length, exchangeable inlay sole provides the highest possible comfort in safety shoes.
- The inlay sole is functionally absorbing and releasing moisture and thus provides for a pleasant foot climate.
- Antistatic

INSOLE

Antistatic soft-fleece
insole

Antistatic, even if 100 % dry, without using additional means fulfilling a bridge function to the outsole.

- Approximately 50 % lighter than comparable soles made of natural materials
- Flexible and shape-retaining
- Good air permeability
- Excellent wear resistance
- High moisture absorption
- Quick drying (virtually overnight)

PENETRATION RESISTANCE

Steel midsole

Best possible protection from below: The corrosion-resistant midsole made of stainless steel complies with the penetration safety standard EN 12568 and furthermore fulfils the additional requirements for penetration protection in accordance with EN ISO 20344 / 20345. Particularly recommendable when working in areas where there is an increased risk of injuries due to pointed or sharp objects, such as in the construction industry.

OUTSOLE

SAFETY-GRIP deep-treaded double-density sole with profile



- S-line shaped configuration of the tread blocks, for an ergonomic foot roll
- Excellent slip resistance
- Antistatic

Outsole: Rubber

- Colour: black
- Profile depth: 6.0 mm
- Particularly abrasion-resistant
- Heat-resistant to approx. 200°C, for short periods to 300°C
- Flexible at cold temperatures to approx. -20°C
- Oil and fuel resistant
- Resistant to a large number of chemicals (acids and alkalis)
- Notch-resistant

Midsole: PU (polyurethane)

- The soft PU core provides a good impact absorption and high wearing comfort