



Transport equipment

Product data sheet

Article no.: 8583-3 Parcel cart with double wing doors



Made of tubular and sectional steel, welded and powder coated blue RAL 5007, bolted construction. Ends and 1 side made of wire lattice 100 x 100 x 5 mm. With double wing doors at the open side panel. Tubular steel frame with wire lattice 100 x 100 x 5 mm. Integrated bolt lock, doors lockable with padlock (not included in delivery), wing doors turnable till side panels. Platform made of special wood material boards, surface beech grain. Wheels: 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with precision deep groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	600
Length of usable platform (mm)	1200
Width of usable platform (mm)	800
Height of loading platform (mm)	269
Total length (mm)	1369
Total width (mm)	830
Total height (mm)	1800
Tyres	TPE
Wheel size (mm)	200 x 40
Version	mit Türen
Weight (kg)	73
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976858333