


Transport equipment

Product data sheet

Article no.: 92910 ESD-storage trolley



Electrostatic discharge construction (ESD = Electrostatic Discharge). Tubular steel and sectional steel welded, conductive powder coating, slate grey RAL 7015. 2 swivel and 2 fixed-wheel castors. Wheels electrically conductive (anti-static) with TPE-ESD tyres (thermoplastic elastomer). Hubs with precision deep groove ball bearing. Maximum comfort: Very low starting, rolling and swivelling resistance. Low noise operation on level floors. Tyres are non-marking. 2 swivel castors with wheel lock, according to the European Standard EN 1757-3 (safety of platform trolleys). Open frames without boards. With tiltable platforms. Upper and middle platforms tiltable to both sides by 15° and 30°, locked by spring catch. Capacity upper and middle shelves 50 kg.

Technical Details:



Total load capacity (kg)	200
Length of usable platform (mm)	605
Width of usable platform (mm)	405
Shelf heights (mm)	197, 652, 1152
Load capacity per shelf (kg)	50
Total length (mm)	821
Total width (mm)	455
Total height (mm)	1178
Tyres	TPE-ESD
Wheel size (mm)	125 x 32
Weight (kg)	26
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976929101