

TECHNICAL DATA SHEET

SCOTT ESD S1 No. 71872


Sz. 35 - 48



LABELLING ACCORDING TO STANDARD

| | |
|--|---|
| Standard for safety footwear EN ISO 20345:2022 S1 | Basic requirement for S1: A Antistatic shoe - E Energy absorption in the heel - Closed heel area |
| Additional requirements | FO FUEL RESISTANCE SR SLIP RESISTANCE on ceramic tile with glycerine. |



FORM


| | |
|--|--|
| Safety sandal  | Form A - in size 42, the upper height must not exceed 11.2 cm. |
|--|--|

AREAS OF APPLICATION

| | |
|----------------------|--|
| Areas of application | Dry work areas Industry, storage, transport, assembly etc. (S1) Areas where there is a risk of electrostatic discharge (ESDS/ESD) E.g. airports, airplane construction, automobile manufacturing No scratches from metal parts Close to induction loops / metal detectors |
|----------------------|--|

FEATURES

| | | |
|--|--|---|
| ESD equipment | Thanks to its excellent discharge capability, the shoe is suitable for work in ESD sensitive or electrostatically protected areas (EPA). The shoes comply to the standard 61340-5-1. |  |
| Sizes (unisex model) | <ul style="list-style-type: none"> Expanded size range: available in sizes 35 - 48 | |
| Certification in accordance with DGUV rule 112-191 | <ul style="list-style-type: none"> Certified for orthopaedic inserts |  |

| FEATURES | |
|--------------------------|--|
| Low weight | <ul style="list-style-type: none"> • Use of a composite toe cap and a metal-free puncture protection • Comfortable |
| Padded upper edge | <ul style="list-style-type: none"> • Excellent wearing comfort: the padded upper edge protects the Achilles tendon. |
| Padded tongue | <ul style="list-style-type: none"> • Excellent wearing comfort: The tongue prevents pressure marks. |
| Reflective material | <ul style="list-style-type: none"> • Good visibility in the dark  |
| Hook-and-pile fastener | <ul style="list-style-type: none"> • Can be opened and closed easily and quickly • Individually adjustable for optimal adaptation to the foot • Improves the comfort and fit |
| Heel loop | <ul style="list-style-type: none"> • Quicker into the shoe: The heel loop makes it easier to get inside the shoe |
| No metal or leather | <ul style="list-style-type: none"> • Low weight • Suitable for work areas sensitive to metal • Does not trigger metal detectors • Use around induction loops is possible • Suitable for persons allergic to leather |
| UPPER MATERIAL | |
| Microfibre | <ul style="list-style-type: none"> • Synthetic material • Particularly soft • Retains its shape • Tear-resistant • Quick drying • Abrasion-resistant and light |
| Textile material | <ul style="list-style-type: none"> • Areas of application S1 • Synthetic material • Retains its shape • Tear-resistant • Quick drying • Abrasion resistant and light |
| LINING | |
| Breathable fabric lining | <ul style="list-style-type: none"> • Climate-regulating • Good ventilation • Skin-friendly • High absorption and emission of moisture |
| Heel pocket lining | <ul style="list-style-type: none"> • The abrasion-resistant microfibre material is particularly sturdy and provides for a pleasant wearing comfort. |

TOE PROTECTION CAP


Composite toe cap



- Protection against impacts of min. 200 joules and pressure loading of min. 15 kN
- Permanent edge coverage for cushioning
- Ergonomically shaped
- Comfortable toe room
- Good coverage of the little toe area
- Low weight - weighs less than conventional steel caps
- 100% metal-free
- 100% anti-magnetic

INLAY SOLE

Full-length inlay sole
ESD PRO (rec)



- ESD EQUIPMENT: Protection against electrostatic discharge (ESD). The full-length, exchangeable inlay sole is conductive and designed for the use in ESD safety footwear according to the standards DIN EN ISO 20345 and DIN EN 61340-5-1.
- Inlay sole with recycled material content
- The full-length, exchangeable inlay sole provides the highest possible comfort in safety shoes.
- The inlay sole is functionally absorbing and releasing moisture and thus provides for a pleasant foot climate.
- The extreme softness of the PU foam absorbs shocks on impact and increases walking comfort.
- Improvement of the shoe climate thanks to the PU foam's open cell structure. So the foot is always kept comfortably dry.

INSOLE

ESD soft-fleece insole

ESD equipment: Protection against electrostatic discharge (ESD), and without using additional means fulfilling a bridge function to the outsole.

- Approximately 50 % lighter than comparable soles made of natural materials
- Flexible and shape-retaining
- Good air permeability
- Excellent wear resistance
- High moisture absorption
- Quick drying (virtually overnight)

OUTSOLE

TRAINERS double-density sole with profile



- Excellent slip resistance
- Antistatic

Outsole: TPU (thermoplastic polyurethane)

- Colour: translucent
- Profile depth: 4.0 mm
- Particularly abrasion-resistant
- Heat-resistant to approx. 130°C
- Flexible at cold temperatures to approx. -30°C
- Oil and fuel resistant

Midsole: PU (polyurethane)

- The soft PU core provides a good impact absorption and high wearing comfort