

TECHNICAL DATA SHEET

VINTAGE Pirate Low ESD S3 No. 722071


Sz. 37 - 47



LABELLING ACCORDING TO STANDARD

| | |
|---|---|
| Standard for safety footwear EN ISO 20345 S3 | Basic requirement for S3: A Antistatic shoe - E Energy absorption in the heel - FO Fuel resistance - WRU Water penetration and water absorption resistant upper - P Penetration resistance - Closed heel area - Profiled outsole |
| Additional requirements | SRC Slip resistance: Slip resistant on floors of ceramic tiles with a sodium lauryl sulfate (SLS) solution and on steel floors with glycerol. When it comes to slip resistance as defined by EN ISO 20345, SRC signifies the best possible rating a safety shoe can reach. |



FORM

| | |
|--|--|
| Safety shoe  | Form A - in size 42, the upper height must not exceed 11.2 cm. |
|--|--|

AREAS OF APPLICATION

| | |
|----------------------|--|
| Areas of application | Indoors and outdoors Areas where exposure to moisture is expected (S2) Areas where there is a risk of penetration from pointed and sharp objects (S3) Areas where there is a risk of electrostatic discharge (ESDS/ESD) |
|----------------------|--|


FEATURES

| | |
|--|--|
| ESD equipment | Thanks to its excellent discharge capability, the shoe is suitable for work in ESD sensitive or electrostatically protected areas (EPA). The shoes comply to the standard 61340-5-1.  |
| Sizes (unisex model) | <ul style="list-style-type: none"> Expanded size range: available in sizes 37 - 47 |
| Certification in accordance with DGUV rule 112-191 | <ul style="list-style-type: none"> Certified for orthopaedic inserts  |


FEATURES

| | |
|-----------------------------------|---|
| Low weight sole | <ul style="list-style-type: none"> • Comfortable |
| Padded upper edge | <ul style="list-style-type: none"> • Excellent wearing comfort: the padded upper edge protects the Achilles tendon. |
| Full, padded bellows tongue | <ul style="list-style-type: none"> • Excellent wearing comfort: The tongue prevents pressure marks and avoids dirt from entering into the shoe. |
| Abrasion-resistant toe protection | <ul style="list-style-type: none"> • Directly applied to the upper in the shoe tip area • Excellent wear protection in the shoe tip area • Protects the upper in this critical area against premature wear |


UPPER MATERIAL

| | |
|--|--|
| Waxy cowhide leather with vintage style | <ul style="list-style-type: none"> • Areas of application S2/S3 • Natural material • Waxed • Wear-resistant • Breathable • Water penetration/absorption in accordance with EN ISO 20345 S2 |
| Sustainably produced leather  | <ul style="list-style-type: none"> • Manufactured in Germany according to high social and ecological standards |

LINING


| | |
|--|---|
| Fabric lining BIOACTIVE  | <ul style="list-style-type: none"> • Climate-regulating • High breathability • Skin-friendly • High degree of moisture absorption and release |
| Heel pocket lining | <ul style="list-style-type: none"> • The abrasion-resistant microfibre material is particularly sturdy and provides for a pleasant wearing comfort. |

TOE PROTECTION CAP

| | |
|--|--|
| Steel toe cap  | <ul style="list-style-type: none"> • Protection against impacts of min. 200 joules and pressure loading of min. 15 kN • Permanent edge coverage for cushioning • Ergonomically shaped • Comfortable toe room • Good coverage of the little toe area |
|--|--|

INLAY SOLE

Full-length inlay sole
ESD PRO



- ESD EQUIPMENT: Protection against electrostatic discharge (ESD). The full-length, exchangeable inlay sole is conductive and designed for the use in ESD safety footwear according to the standards DIN EN ISO 20345 and DIN EN 61340-5-1.
- The full-length, exchangeable inlay sole provides the highest possible comfort in safety shoes.
- The inlay sole is functionally absorbing and releasing moisture and thus provides for a pleasant foot climate.
- The extreme softness of the PU foam absorbs shocks on impact and increases walking comfort.
- Improvement of the shoe climate thanks to the PU foam's open cell structure. So the foot is always kept comfortably dry.

PENETRATION RESISTANCE

Metal-free penetration
protection

The textile midsole complies with the penetration safety standard EN 12568 and furthermore fulfils the additional requirements for penetration protection in accordance with EN ISO 20344 / 20345. The light and flexible material enables an increased elasticity of the shoe, which can particularly be recognized when working on uneven grounds or on your knees.

The textile variant offers 100 % foot coverage compared to steel midsoles (foot coverage 85 % due to limits in the shoe manufacturing process). Being 100 % metal-free and antimagnetic, this equipment is used as penetration protection in safety shoes.

OUTSOLE

PIRATE double-density
sole with profile



- Red contrasts in form of a skull
- Excellent slip resistance
- Antistatic

Outsole: Rubber

- Colour: black, with coloured inserts
- Profile depth: 3.0 mm
- Particularly abrasion-resistant
- Heat-resistant to approx. 200°C, for short periods to 300°C
- Flexible at cold temperatures to approx. -20°C
- Oil and fuel resistant
- Resistant to a large number of chemicals (acids and alkalis)

Midsole: PU (polyurethane)

- The soft PU core provides a good impact absorption and high wearing comfort